



# StoreSet

## SM505T LED66S/830 PSD-VLC MB SI

StoreSet track, 830 warm white, Power supply unit with DALI interface, Medium beam, Silver

Today's retail destinations are all about creating experiences that attract and retain customers. StoreSet adds atmosphere to your store by introducing contrast and breaking up the traditional continuous lines of light. A variety of beam shapes, combined with excellent light quality, ensures your merchandise has great stand out, at the same time as enabling you to create a variety of different ambiances. Each StoreSet panel is lightweight and can be easily connected to power tracks or a Maxos fusion backbone. Installation is straightforward, and if your needs change, you can simply adapt the lighting by repositioning the panels and luminaires along the track or trunk. This makes StoreSet a truly flexible, non-linear tool for creating store ambiances that sell.

### Warnings and Safety

- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents.

### Product data

General Information			
Light source replaceable	No	Service tag	Yes
Number of gear units	1 unit	Product family code	SM505T [StoreSet track]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s

EU RoHS compliant	Yes
-------------------	-----

#### Light Technical

Luminous Flux	6,600 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	132 lm/W
Color rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Medium beam
Luminaire light beam spread	38°
Unified glare rating CEN	Not applicable

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.280 ms
Power Consumption	50 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

#### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide

Housing Color	Silver
Optical cover finish	Clear
Overall length	613 mm
Overall width	184 mm
Overall height	75 mm
Dimensions (Height x Width x Depth)	75 x 184 x 613 mm

#### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

#### Product Data

Order product name	SM505T LED66S/830 PSD-VLC MB SI
Full product name	SM505T LED66S/830 PSD-VLC MB SI
Full product code	871869917238100
Order code	910500459763
Material Nr. (12NC)	910500459763
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699172381
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699172381

Dimensional drawing

