



StoreSet

SM505S LED90S/830 PSD-CLO-VLC DA25N BK

StoreSet trunking, 830 warm white, Power supply unit with DALI interface and constant light output, Double asymmetric optic 25° narrow beam, Black

Today's retail destinations are all about creating experiences that attract and retain customers. StoreSet adds atmosphere to your store by introducing contrast and breaking up the traditional continuous lines of light. A variety of beam shapes, combined with excellent light quality, ensures that your merchandise stands out, at the same time as enabling you to create a variety of different ambiances. Each StoreSet panel is lightweight and can be easily connected to power tracks or a Maxos fusion backbone. Installation is straightforward, and if your needs change, you can simply adapt the lighting by repositioning the panels and luminaires along the track or trunk. This makes StoreSet a truly flexible, non-linear tool for creating store ambiances that sell.

Warnings and Safety

- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents.

Product data

General Information		
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and,	for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
		Product family code SM505S [StoreSet trunking]
		Lighting Technology LED
		Value ladder Specification
		CE mark Yes
		Warranty period 5 years

Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	9,000 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	122 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	830 warm white
Optic type	Double asymmetric optic 25° narrow beam
Luminaire light beam spread	72° x 90°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	59 W
Average CLO power consumption	66.4 W
End CLO power consumption	73.8 W
Inrush current	22 A
Inrush time	0.275 ms
Power Consumption	74 W
Power Factor (Fraction)	0.9
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface and constant light output
Control interface	DALI
Constant light output	Yes

Mechanical and Housing

Housing material	Plastic
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate

Fixation material	Steel
Housing Colour	Black
Optical cover/lens finish	Clear
Overall length	575 mm
Overall width	184 mm
Overall height	89 mm
Dimensions (height x width x depth)	89 x 184 x 575 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	SM505S LED90S/830 PSD-CLO-VLC DA25N BK
Full product name	SM505S LED90S/830 PSD-CLO-VLC DA25N BK
Full EOC	871869917246600
Order code	17246600
Material no. (12 NC)	910500459771
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699172466
Numerator – packs per outer box	1
EAN/UPC – Case	8718699172466

StoreSet

Dimensional drawing

