



SlimBlend

Rectangular, recessed

RC400B LED36S/830 PSD W30L120 VPC PIP

SlimBlend recessed mod. 600, 830 warm white, Power supply unit with DALI interface, Push-in connector and pull relief, Safety class II

Office regulation-compliant lighting with good quality of light is in demand. Moreover, there is also an increasing need for comfort-enhancing effects such as diffused lighting and lighting that smoothly blends into the ceiling architecture. That's why 'surface of light' solutions are becoming more and more popular. But parallel to these needs, are the demands to reduce energy and maintenance costs. SlimBlend answers all these needs and more. Not only does it provide glare-free comfort with a diffuse effect and clutter-free aesthetics, thanks to integrated control options, it also creates a special blending of light. It uses the 'trapped' light under the masking to create a subtle glow, with a soft transition to the edge, lowering the brightness perception and blending the light into the ceiling. SlimBlend can also be part of a connected lighting system and integrated into the IT infrastructure, enabling data on usage to be collected to help reduce energy costs and enhance employee comfort further. Also, thanks to the slim design, it enables technical equipment to be more easily installed in the plenum. Moreover, thanks to the variety of ways of mounting, various ceiling-mounted lights can take advantage of this luminaire family. SlimBlend comes in square and rectangular and can be either recessed, surface-mounted or suspended. It offers a good balance between initial cost and ROI, making it the ideal choice for delivering excellent quality of light and a fast ROI for offices.

Product data

SlimBlend Rectangular, recessed

| | |
|--|--|
| General Information | |
| Light source replaceable | No |
| Number of gear units | Unit |
| Driver included | Yes |
| Remarks | *- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. |
| Product family code | RC400B [SlimBlend recessed mod. 600] |
| Lighting Technology | LED |
| Value ladder | Specification |
| CE mark | Yes |
| Warranty period | 5 years |
| Flammability mark | For mounting on normally flammable surfaces |
| ENEC mark | ENEC mark |
| Glow-wire test | Temperature 650 °C, duration 5 s |
| EU RoHS compliant | Yes |
| Light Technical | |
| Luminous Flux | 3,600 lm |
| Correlated Colour Temperature | 3000 K |
| Luminous efficacy (rated) (nom.) | 97 lm/W |
| Colour rendering index (CRI) | 80 |
| Beam angle of light source | 120 degree(s) |
| Light source colour | 830 warm white |
| Optic type | - |
| Luminaire light beam spread | 120° |
| Unified Glare Rating (CEN) | 19 |
| Operating and Electrical | |
| Input Voltage | 220–240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 20.4 A |
| Inrush time | 0.195 ms |
| Power Consumption | 37 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Push-in connector and pull relief |
| Cable | - |
| Number of products on MCB of 16 A type B | 24 |
| Temperature | |
| Ambient temperature range | +10 to +40 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Driver/power unit/transformer | Power supply unit with DALI interface |

| | |
|--|---------------------------------------|
| Control interface | DALI |
| Constant light output | No |
| Mechanical and Housing | |
| Housing material | Stainless steel |
| Reflector material | - |
| Optic material | Polymethyl methacrylate |
| Optical cover/lens material | Polymethyl methacrylate |
| Fixation material | - |
| Housing Colour | White |
| Optical cover/lens finish | Textured |
| Overall length | 1,197 mm |
| Overall width | 297 mm |
| Overall height | 52 mm |
| Dimensions (height x width x depth) | 52 x 297 x 1197 mm |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Protection class IEC | Safety class II |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.43, 0.40) SDCM<3 |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Control gear failure rate at median useful life 50,000 h | 5 % |
| Lumen maintenance at median useful life* 50,000 h | L80 |
| Application Conditions | |
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level | 1% |
| Suitable for random switching | Yes |
| Product Data | |
| Order product name | RC400B LED36S/830 PSD W30L120 VPC PIP |
| Full product name | RC400B LED36S/830 PSD W30L120 VPC PIP |
| Full EOC | 871869917467500 |
| Order code | 17467500 |
| Material no. (12 NC) | 910500459911 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8718699174675 |
| Numerator – packs per outer box | 1 |
| EAN/UPC – Case | 8718699174675 |

SlimBlend Rectangular, recessed

Dimensional drawing

