



# StyliD

## ST740S LED20S/827 PSU NB WH

StyliD Comp. Maxos fusion, 827 warm white, Power supply unit (On/Off), Narrow beam, White

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain the quality of light they are used to, flexibility in architectural integration, and the right light effects to catch the customer's eye. Last but not least, they need future-proof solutions that will enable them to implement differentiating concepts in their store. Delivering high-quality light, punch in the beam and outstanding luminous efficacy, StyliD is the ideal energy-efficient solution for today's demanding retail environments, covering a variety of lighting applications, with including CrispWhite for fashion stores and Food recipes for supermarkets.

### Product data

General Information			
Light source replaceable	No	Warranty period	5 years
Number of gear units	Unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
Product family code	ST740S [StyliD Comp. Maxos fusion]	EU RoHS compliant	Yes
Lighting Technology	LED	Light Technical	
CE mark	Yes	Luminous Flux	1,950 lm
		Correlated Colour Temperature	2700 K
		Luminous efficacy (rated) (nom.)	99.48979591836734 lm/W
		Colour rendering index (CRI)	≥80
		Beam angle of light source	120 degree(s)
		Light source colour	827 warm white
		Optic type	Narrow beam

Luminaire light beam spread	10°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.25 ms
Power Consumption	19.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	34

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing material	Metal-Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	172 mm
Overall width	84 mm
Overall height	184 mm

Dimensions (height x width x depth)	184 x 84 x 172 mm
-------------------------------------	-------------------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.45, 0.41) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

Product Data

Order product name	ST740S LED20S/827 PSU NB WH
Full product name	ST740S LED20S/827 PSU NB WH
Full EOC	871869917805500
Order code	17805500
Material no. (12 NC)	910500465015
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699178055
Numerator – packs per outer box	1
EAN/UPC - Case	8718699178055

Dimensional drawing



