



# EcoStyle

## ST440T LED27S/CH PSU WB BK

EcoStyle track mounting, Champagne, Power supply unit (On/Off), Wide beam, Safety class II, White

Retailers are looking for an affordable LED accent-lighting solution with a reasonable payback compared to conventional technologies. Now, thanks to EcoStyle, they need look no further. With a LED light source and dedicated reflector system, EcoStyle delivers powerful, good-quality accent lighting, enabling retailers to display their merchandise in the best possible light. For food and fashion retailers, EcoStyle is available with special light recipes to further enhance the store ambience and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambience; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambience; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright. The track-mounted EcoStyle is also available in a choice of black or white finish. And the combination of efficient LED technology and an innovative heatsink ensures that this is a reliable, lasting solution.

### Product data

General Information		
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
		Service tag
		Yes
		Product family code
		ST440T [EcoStyle track mounting]
		Lighting Technology
		LED
		CE mark
		Yes
		Warranty period
		5 years
		Flammability mark
		For mounting on normally flammable surfaces
		ENEC mark
		ENEC mark
		Glow-wire test
		Temperature 650 °C, duration 5 s

EU RoHS compliant	Yes
-------------------	-----

#### Light Technical

Luminous Flux	2,600 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	110.63829787234043 lm/W
Color rendering index (CRI)	80
Beam angle of light source	120 degree(s)
Light source color	Champagne
Optic type	Wide beam
Luminaire light beam spread	36°

#### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.25 ms
Power Consumption	23.5 W
Power Factor (Fraction)	0.95
Connection	-
Cable	-
Number of products on MCB of 16 A type B	34

#### Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

#### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	Polyamide
Housing Color	White

Optical cover finish	Clear
Overall length	189 mm
Overall width	112 mm
Overall height	193 mm
Dimensions (Height x Width x Depth)	193 x 112 x 189 mm

#### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.4578, 0.4101) SDCM <3
Power consumption tolerance	+/-10%

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

#### Product Data

Order product name	ST440T LED27S/CH PSU WB BK
Full product name	ST440T LED27S/CH PSU WB BK
Full product code	871869939942900
Order code	910500465321
Material Nr. (12NC)	910500465321
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699399429
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699399429

## Dimensional drawing

