



# GentleSpace Gen3

## BY481X LED250S/840 WB GC SI ACW-L BR

Gentlespace gen3 Interact, 840 neutral white, Power supply unit with DALI interface, Wide beam, Silver RAL 9006

The GentleSpace gen3 provides a smart combination of versatility with high efficiency, connectivity options and reliability. It provides a wide variety of optics, beam angles (from very narrow to wide) and lumen packages, each delivering best-in-class quality of light for enhanced safety, productivity and comfort. With the GentleSpace gen3 you can easily create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It supports changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. Additionally, a choice of mounting possibilities and a pre-mounted IP65 connector enables quick-and-easy installation. You can choose various cover materials and special variants for extreme temperatures (XT), hazardous areas (ATEX 2/22) or sports applications. In addition, the GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to an IoT-based system and software applications, such as Interact Industry. Created with circularity principles in mind, the GentleSpace is a serviceable luminaire with all the information available via the Signify ServiceTag app. Whether you are looking for a reliable 'fit & forget' solution or one that can be adapted and controlled after installation, the GentleSpace gen3 is the ideal solution for your application.

### Product data

General Information		Value ladder	Specification
Light source replaceable	Yes	CE mark	Yes
Number of gear units	Unit	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on easily flammable surfaces
Product family code	BY481X [Gentlespace gen3 Interact]	ENEC mark	ENEC mark
Lighting Technology	LED		

# GentleSpace Gen3

Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	25,000 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	154 lm/W
Colour rendering index (CRI)	>80
Beam angle of light source	114 degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	42° x 44°
Unified Glare Rating (CEN)	Not applicable

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	160 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

## Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Colour	Silver RAL 9006
Optical cover/lens finish	Clear
Overall length	712 mm
Overall width	490 mm

Overall height	120 mm
Dimensions (height x width x depth)	120 x 490 x 712 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.5 %
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

## Application Conditions

Performance ambient temperature Tq	45 °C
Maximum dim level	10%
Suitable for random switching	Yes

## Product Data

Order product name	BY481X LED250S/840 WB GC SI ACW-L BR
Full product name	BY481X LED250S/840 WB GC SI ACW-L BR
Full EOC	871869940737700
Order code	40737700
Material no. (12 NC)	910500465543
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699407377
Numerator – packs per outer box	1
EAN/UPC – Case	8718699407377

## GentleSpace Gen3

### Dimensional drawing

