



GentleSpace Gen3

BY481P LED250S/840 PSD NBA GC SI

GentleSpace Gen3 - - 840 neutral white - Power supply unit with DALI interface - Wide beam - PMMA bowl/cover - Silver

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

Product data

General Information			
Lamp family code	-	Optic type	WB [Wide beam]
Beam angle of light source	114 °	Optical cover/lens type	PM [PMMA bowl/cover]
Light source colour	840 neutral white	Luminaire light beam spread	-
Cap base	- [-]	Control interface	DALI
Light source replaceable	Yes	Connection	W5 [Plug-in connector 5-pole Wieland/ Adels compatible]
Number of gear units	1 unit	Cable	Cord with plug Wieland/Adels compatible 5-pole
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	Protection class IEC	Safety class I (I)
Driver included	Yes	Glow-wire test	850/5 [Temperature 850 °C, duration 5 s]

GentleSpace Gen3

Flammability mark	D [For mounting on easily flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Constant light output	No
Number of products on MCB	12
RoHS mark	RoHS mark
Product Family Code	BY480P [GentleSpace Gen3]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Average CLO power consumption	- W W
Inrush current	4.8 A
Inrush time	2.3 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	600 mm
Overall width	490 mm
Overall height	110 mm
Diameter	-
Colour	Silver

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]

Initial Performance (IEC Compliant)

Initial luminous flux	25000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	154 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	160 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Median useful life L70B50	100000 h
Median useful life L80B50	70000 h
Median useful life L90B50	50000 h
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	45 °C
Maximum dimming level	10%
Suitable for random switching	No


Product Data

Full product code	871869941465800
Order product name	BY481P LED250S/840 PSD NBA GC SI
EAN/UPC – product	8718699414658
Order code	41465800
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910500465803
Net weight (piece)	12.000 kg



GentleSpace Gen3

Dimensional drawing



GentleSpace gen3 BY480P-BY483P

