



# TownGuide Performer

## BDP100 LED100/830 DW PCF SI CLO 62P

TOWNGUIDE PERF FLAT CONE - LED module 10000 lm -  
 Distribution wide - Polycarbonate bowl/cover frosted -  
 Constant light output - Post-top for diameter 62 mm

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

### Product data

General Information		Driver/power unit/transformer	PSR-CLO [ Power supply unit regulating with constant light output]
Number of light sources	6 [ 6 pcs]	Driver included	Yes
Lamp family code	LED100 [ LED module 10000 lm]	Optical cover/lens type	PCF [ Polycarbonate bowl/cover frosted]
Light source colour	830 warm white	Luminaire light beam spread	50° x 70°
Light source replaceable	Yes	Embedded control	CLO [ Constant light output]
Number of gear units	1 unit	Control interface	-

# TownGuide Performer

Light regulation	-
Cable	-
Protection class IEC	Safety class I (I)
Parts colour	All parts colored
Coating	-
Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Flammability mark	NO [ -]
Safety device	PCBC [ PCB cover]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Outdoor optic type	Distribution wide
Photocell	No [ -]
Constant light output	Yes
Number of products on MCB	10
RoHS mark	RoHS mark
WEEE mark	-
LED engine type	LED
Product Family Code	BDP100 [ TOWNGUIDE PERF FLAT CONE]

## Light Technical

Upward light output ratio	3
Standard tilt angle post-top	0°
Standard tilt angle side entry	-

## Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	67 W
Average CLO power consumption	71 W
End CLO power consumption	76 W
Inrush current	47 A
Inrush time	0.250 ms
Power factor (min.)	0.99
Power factor (nom.)	0.94

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Mounting device	62P [ Post-top for diameter 62 mm]
Optical cover/lens shape	Conical flat
Optical cover/lens finish	Frosted
Torque	15
Overall height	209 mm

Overall diameter	570 mm
Effective projected area	0.051 m <sup>2</sup>
Colour	Silver

## Approval and Application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]

## Initial Performance (IEC Compliant)

Initial luminous flux	4346 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	62 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	80
Initial chromaticity	(0.43, 0.40) SDCM <5
Initial input power	76 W
Power consumption tolerance	+/-11%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life	0.001 %
100000 h	
Lumen maintenance at median useful life*	-
35000 h	
Lumen maintenance at median useful life*	-
50000 h	
Lumen maintenance at median useful life*	-
75000 h	
Lumen maintenance at median useful life*	82
100000 h	

## Application Conditions

Ambient temperature range	-40 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable

## Product Data

Full product code	871829191056500
Order product name	BDP100 LED100/830 DW PCF SI CLO 62P
EAN/UPC – product	8718291910565
Order code	91056500
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910500991117
Net weight (piece)	6.480 kg


# TownGuide Performer

## Dimensional drawing




TownGuide Performer BDP100-105

## Photometric data



OFPL1\_BDP100PCF1xECO100830DW



OFPC1\_BDP100PCF1xECO100830DW

