

SmartForm TBS417

TBS417 1x54W/840 HFP MLO-PC W

SmartForm recessed semi-modular, 1, 54 W, 840 neutral white, HF Performer, Micro-lens optic in polycarbonate cover, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m^2 is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

Product data


General Information		Product family code	TBS417 [SmartForm recessed semi-modular]
Lamp family code	TL5 [TL5]	Embedded control	-
Cap-Base	G5 [G5]	CE mark	Yes
Gear	HFP [HF Performer]	ENEC mark	ENEC mark
Feed-through wiring	-		

SmartForm TBS417

Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Optical cover type	Micro-lens optic in polycarbonate cover
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	54 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Mechanical and Housing	
Housing Color	White
Overall length	1,208 mm
Approval and Application	
Ingress protection code	IP40 [Wire-protected]

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBS417 1x54W/840 HFP MLO-PC W
Full product name	TBS417 1x54W/840 HFP MLO-PC W
Full product code	871794398819800
Order code	910501903103
Material Nr. (12NC)	910501903103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943988198
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943988198

Dimensional drawing



Product	A
TBS417 1x54W/840 HFP MLO-PC W	1,208 mm

