



# SmartForm TBS415

## TBS415 1x35W/830 HFP D8-VH W AIR

SmartForm recessed semi-modular, 1, 35 W, 830 warm white, HF Performer, Semi-high-gloss optic 3D micro-lamellae very high reflectance, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption ( $W/m^2$  is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO2 levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS415 – 'light beam' semi-modular – 600 mm module. SmartForm recessed luminaires are designed for integration in linear ceiling systems with a width of 148 mm (half module 300 mm) for exposed and concealed T-bar and the extended versions for bandraaster ceilings. 'Light surface' TBS415 1-lamp. MLO and asymmetrical optic in 1/2 modular concept, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. 'Light beam' TBS415 1-lamp: micro-optics in 1/2 modular concept with AIR function, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. 'Light beam' TBS415 2-lamps. Mini-optics, 2-lamps in 1/2 modular concept with AIR function, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm.

### Product data

# SmartForm TBS415

## General Information

Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Feed-through wiring	-
Product family code	TBS415 [SmartForm recessed semi-modular]
Embedded control	-
CE mark	Yes
Glow-wire test	Temperature 850 °C, duration 5 s

## Light Technical

Number of light sources	1
Light source color	830 warm white
Optic type	Semi-high-gloss optic 3D micro-lamellae very high reflectance
Optical cover type	-

## Operating and Electrical

Input Voltage	220 to 240 V
Power Consumption	35 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-

## Mechanical and Housing

Housing Color	White
---------------	-------

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

## Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

## Product Data

Order product name	TBS415 1x35W/830 HFP D8-VH W AIR
Full product name	TBS415 1x35W/830 HFP D8-VH W AIR
Full product code	871794398902700
Order code	910501911403
Material Nr. (12NC)	910501911403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943989027
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943989027

## Dimensional drawing

