

SmartForm TBS411

TBS411 1x28W/840 HFP C8-VH W SC

SmartForm recessed semi-modular, 1, 28 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae very high reflectance, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO2 levels, making SmartForm an environmentally friendly choice. These slender SmartForm recessed luminaires are designed for integration in variety of linear ceiling systems: exposed and concealed T-bar, plaster and the extended versions for bandrastr ceilings. Micro-optics and covers (MLO-PC and Opal) in smallest concept, width 90 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. Micro-optics and covers in smallest concept with AIR function, width 100 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. Mini-optics, 2-lamps, width 115 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm.

Product data

General Information	
Lamp family code	TL5 [TL5]

Gear	HFP [HF Performer]
Feed-through wiring	-

SmartForm TBS411

Product family code	TBS411 [SmartForm recessed semi-modular]
Embedded control	-
CE mark	Yes
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical

Number of light sources	1
Light source color	840 neutral white
Optic type	High-gloss optic 3D micro-lamellae very high reflectance
Optical cover type	-

Operating and Electrical

Input Voltage	220 to 240 V
Power Consumption	28 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-

Mechanical and Housing

Housing Color	White
Overall length	1,197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I


Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Order product name	TBS411 1x28W/840 HFP C8-VH W SC
Full product name	TBS411 1x28W/840 HFP C8-VH W SC
Full product code	871794399040500
Order code	910501925203
Material Nr. (12NC)	910501925203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943990405
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943990405

Dimensional drawing



Product	A
TBS411 1x28W/840 HFP C8-VH W SC	1,197 mm

