



Cleanroom LED

CR434B LED48/840 PSD W60L60 AC-MLO PI

Led Cleanroom mod. 600 lay-in, LED Module 4800 lm, 840 neutral white, Power supply unit with DALI interface, Acrylate micro-lens optic, Push-in connector 5-pole

Customers operating highly hygienic facilities require special IP65, easy-to-clean, dust-free luminaires that meet all lighting requirements and norms. Moreover, to ensure the integrity of these areas (and stay within budget), they also need to minimize costly downtime and maintenance. With the latest LED engine on board, this LED cleanroom luminaire represents the ideal solution, delivering market-leading energy performance – far beyond fluorescent solutions – over 50,000 hours of maintenance-free operation. This means extremely low operational cost over the total lifetime of the luminaire, and so an excellent financial return on investment.

Product data

General Information			
Lamp family code	LED48 [LED Module 4800 lm]	Product family code	CR434B [Led Cleanroom mod. 600 lay-in]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Specification
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on normally flammable surfaces
Service tag	Yes	ENEC mark	-
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	3,900 lm
		Correlated Color Temperature (Nom)	4000 K

Cleanroom LED

Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Optical cover type	Acrylate micro-lens optic
Luminaire light beam spread	120°
Unified glare rating CEN	16

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.275 ms
Power Consumption	28 W
Power Factor (Fraction)	0.95
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	Aluminum
Optic material	-
Optical cover material	Acrylate
Fixation material	-
Housing Color	White
Optical cover finish	Textured
Overall length	596 mm
Overall width	596 mm

Overall height	74 mm
Dimensions (Height x Width x Depth)	74 x 596 x 596 mm

Approval and Application

Ingress protection code	IP64/65 Dust penetration-protected, splashproof/ Jet-proof
Mech. impact protection code	IK02/05
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	CR434B LED48/840 PSD W60L60 AC-MLO PI
Full product name	CR434B LED48/840 PSD W60L60 AC-MLO PI
Full product code	871794391890400
Order code	910501978103
Material Nr. (12NC)	910501978103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943918904
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943918904

Cleanroom LED

Dimensional drawing

