



# DayZone

## BBS562 LED35S/840 PSD AC-MLO-C ACL W

DayZone recessed square, LED Module, system flux 3500 lm, 840 neutral white, Power supply unit with DALI interface, Acrylate micro-lens optic with circle, ActiLume, Plug-in connector 3-pole Wieland/Adels compatible

For general office lighting, customers want to capture the benefits LED technology has to offer – sustainability and fresh, high-impact design, without compromising visual comfort. Our DayZone recessed LED luminaire delivers high-quality functional lighting with an energy efficiency that matches or even outperforms traditional fluorescent systems. But what makes DayZone really shine is its impressive visual comfort. Our innovative use of LED technology has created a luminaire that breaks away from fluorescent lighting designs of the past to offer a striking appearance and light effect. Glare control and color consistency are compliant with future office norms. DayZone is available in square versions and, to ensure a better fit in plaster ceiling applications, in a round housing.

### Product data

General Information		
Lamp family code	LED35S [LED Module, system flux 3500 lm]	
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Gear	-	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	BBS562 [DayZone recessed square]	
Lighting Technology	LED	
Glow-wire test	Temperature 650 °C, duration 5 s	
Flammability mark	For mounting on normally flammable surfaces	
CE mark	Yes	
ENEC mark	ENEC mark	
Warranty period	5 years	
EU RoHS compliant	Yes	

Embedded control	ActiLume
------------------	----------

## Light Technical

Luminous Flux	3,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Optical cover type	Acrylate micro-lens optic with circle
Luminaire light beam spread	130°
Unified glare rating CEN	Not applicable

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	1 ms
Power Consumption	35 W
Power Factor (Fraction)	0.97
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	24

## Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing Material	Steel
------------------	-------

Reflector material	Aluminum
Optic material	-
Optical cover material	Acrylate
Fixation material	-
Housing Color	White
Optical cover finish	Textured
Overall length	622 mm
Overall width	622 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 622 x 622 mm

## Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

## Product Data

Order product name	BBS562 LED35S/840 PSD AC-MLO-C ACL W
Full product name	BBS562 LED35S/840 PSD AC-MLO-C ACL W
Full product code	871829127303500
Order code	910502004103
Material Nr. (12NC)	910502004103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291273035
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291273035

## Dimensional drawing

