



# PowerBalance RC360B

## RC360B G2 LED34S/840 PSD W60L60 VPC W WH

PowerBalance recessed, LED module, system flux 3400 lm, 840 neutral white, Power supply unit with DALI interface, Plug-in connector 3-pole Wieland/Adels compatible

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability, provided the investment pays back. At the same time, the system should comply with office lighting norms in order to ensure a comfortable working environment. PowerBalance RC360 offers the ideal combination of sustainable performance and return on investment on the one hand, and compliance with relevant office norms on the other. It reduces energy costs by more than half compared to a T5 solution, and the light source also has a longer lifetime. This results in significantly lower operating costs, ensuring a payback that meets the needs of the specification market. The architecture of PowerBalance RC360 enables a range of highly versatile modular and semi-modular luminaires. These can be easily mounted in ceilings with exposed or concealed T-bars, as well as plaster ceilings and bandraaster-type ceilings.

### Warnings and Safety

- The product is IP40 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

### Product data

General Information			
Lamp family code	LED34S [LED module, system flux 3400 lm]	Cap base	- [-]
		Light source replaceable	No

# PowerBalance RC360B

Number of gear units	Unit
Gear	-
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Product family code	RC360B [PowerBalance recessed]
Lighting Technology	LED
Value ladder	Performance
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	3,400 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	124 lm/W
Colour rendering index (CRI)	≥80
Light source colour	840 neutral white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	86°
Unified Glare Rating (CEN)	19

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.255 ms
Power Consumption	27.5 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	20

## Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
----------	-----

Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing material	Steel
Reflector material	Polycarbonate
Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White RAL 9003
Optical cover/lens finish	Matte
Overall length	597 mm
Overall width	597 mm
Overall height	86 mm
Dimensions (height x width x depth)	86 x 597 x 597 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

## Product Data

Order product name	RC360B G2 LED34S/840 PSD W60L60 VPC W WH
Full product name	RC360B G2 LED34S/840 PSD W60L60 VPC W WH
Full EOC	871794311295100
Order code	11295100
Material no. (12 NC)	910502030003
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8717943112951
Numerator – packs per outer box	1
EAN/UPC – Case	8717943112951

## PowerBalance RC360B

### Dimensional drawing

