




PowerBalance Tunable White, recessed

RC464B LED80S/TWH PSD W30L120 VPC W

PowerBalance recessed Tuneable WH, LED Module, system flux 8000 lm, Tunable white, Power supply unit with DALI interface, Plug-in connector 3-pole Wieland/Adels compatible

The right light can have a favourable effect on various physiological processes in the human body. Statistically, 65% of office workers don't feel at their best before 9.00 a.m. By giving them personal control over the lighting in their work space, so they can tailor it to suit the time of day and what they are doing, our PowerBalance Tunable White solution can enhance their comfort, task performance and productivity. Similarly, in schools, PowerBalance Tunable White allows teachers to create the right mood to help pupils to concentrate, relax, etc., depending on the activity at hand, and so perform better overall.

Product data

General Information		luminaire – January 2018*: statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Lamp family code	LED80S [LED Module, system flux 8000 lm]	
Cap base	- [-]	
Light source replaceable	No	
Number of gear units	Unit	
Gear	-	Product family code RC464B [PowerBalance recessed Tuneable WH]
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based	
		Lighting Technology LED

PowerBalance Tunable White, recessed

Embedded control	-
CE mark	Yes
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	8,000 lm
Luminous efficacy (rated) (nom.)	110 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source colour	Tunable white
Optic type	-
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	86°
Unified Glare Rating (CEN)	19

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	1 ms
Power Consumption	73 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Composite materials
Reflector material	Polycarbonate

Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White RAL 9003
Optical cover/lens finish	Matte
Overall length	1,197 mm
Overall width	297 mm
Overall height	79 mm
Dimensions (height x width x depth)	79 x 297 x 1197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31, 0.32) SDCM <3 to (0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	RC464B LED80S/TWH PSD W30L120 VPC W
Full product name	RC464B LED80S/TWH PSD W30L120 VPC W
Full EOC	871869687467700
Order code	87467700
Material no. (12 NC)	910502042803
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696874677
Numerator – packs per outer box	1
EAN/UPC – Case	8718696874677

PowerBalance Tunable White, recessed

Dimensional drawing

