



TrueLine, recessed

RC533B LED19S/830 PSD W8L141 PCV PI5

TrueLine Recessed Line NOC - 1 pc - LED Module, system flux 1900 lm - 830 warm white - Power supply unit with DALI interface - Plaster ceiling version - Width 0.08 m, length 1.41 m - - - Push-in connector 5-pole (PI) - 1410 mm - White - No

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, recessed is able to meet both sets of requirements. TrueLine is also available in a suspended version.

Product data

General Information		Connection	
Number of light sources	1 [1 pc]	Connection	Push-in connector 5-pole (PI)
Lamp family code	LED19S [LED Module, system flux 1900 lm]	Cable	-
Light source colour	830 warm white	Protection class IEC	Safety class I (I)
Cap base	- [-]	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Light source replaceable	No	Flammability mark	F [For mounting on normally flammable surfaces]
Number of gear units	1 unit	Type description	No
Gear	-	CE mark	CE mark
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	ENEC mark	ENEC plus mark
Driver included	Yes	UL mark	-
Optic type	No [-]	Warranty period	5 years
Optical cover/lens type	PM [PMMA bowl/cover]	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance
Luminaire light beam spread	160°		
Embedded control	No [-]		
Control interface	DALI		

TrueLine, recessed

	between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	24
RoHS mark	RoHS mark
Accessory PFC	N/A
Product Family Code	RC533B [TrueLine Recessed Line NOC]
Unified glare rating CEN	25

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	19 A
Inrush time	0.28 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Geometry	Width 0.08 m, length 1.41 m
Housing configuration	PCV [Plaster ceiling version]
Housing material	Steel
Reflector material	-
Optic material	-
Optical cover/lens material	Polycarbonate
Gear tray material	Steel
Fixation material	Steel
Optical cover/lens finish	Opal
Overall length	1409 mm
Overall width	115 mm
Overall height	136 mm
Length	1410 mm
Colour	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	--------------------------

Mech. impact protection code	IK02 [0.2 J standard]
------------------------------	------------------------

Initial Performance (IEC Compliant)

Initial luminous flux	1900 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	101 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.43, 0.40) SDCM<3
Initial input power	18.8 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85

Application Conditions


Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No

Product Data

Full product code	871869906365800
Order product name	RC533B LED19S/830 PSD W8L141 PCV PI5
EAN/UPC – product	8718699063658
Order code	06365800
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910502051603
Net weight (piece)	3.200 kg


TrueLine, recessed

Dimensional drawing




TrueLine recessed RC515B, RC530B-RC534B

Photometric data



IFGU1_RC533BPSDW8L141xLED19S830NOC



IFPC1_RC533BPSDW8L141xLED19S830NOC

