



# Pentura Mini

## TCH128 1xTL5-28W/840 HF

1, TL5, 28 W, 840 neutral white, Electronic high-frequency

Pentura Mini TCH128 is an ultra-slim decorative batten for domestic applications. A cost-effective, ready-to-install mini fluorescent solution. Pentura Mini TCH128 offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. The batten is easy to install e.g. over worktops and workstations in the home, home office and recreational environments, etc. it provides bright light where needed even where installation space is limited. Pentura Mini TCH128 battens are fitted with lamp, tough polycarbonate diffuser and all fixing accessories, reducing installation time to a minimum. The battens are through-wired with removeable end-caps at both ends covering the push-button connection blocks for simple connection and through-wiring.

### Product data


<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	TL5 [TL5]	28 W	
Gear	HF [Electronic high-frequency]	<b>Mechanical and Housing</b>	
CE mark	Yes	Overall length	
Flammability mark	For mounting on normally flammable surfaces	1,223 mm	
Glow-wire test	Temperature 850 °C, duration 5 s	<b>Approval and Application</b>	
<b>Light Technical</b>		Ingress protection code	
Number of light sources	1	IP20 [Finger-protected]	
Light source color	840 neutral white	Protection class IEC	
<b>Operating and Electrical</b>		Safety class II	
Input Voltage		<b>Application Conditions</b>	
220 to 240 V		Suitable for random switching	
		Not applicable	
		<b>Product Data</b>	
		Order product name	
		TCH128 1xTL5-28W/840 HF	

Pentura Mini

Full product name	TCH128 1xTL5-28W/840 HF
Full product code	871155914855799
Order code	910502537718
Material Nr. (12NC)	910502537718
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711559148557
Numerator - Packs per outer box	16
EAN/UPC - Case	8711559804552

Dimensional drawing



Product	A
TCH128 1xTL5-28W/840 HF	1,223 mm

