



Pentura Mini CC

TCH129 1xTL5-14W/840 HF

1, TL5, 14 W, 840 neutral white, Electronic high-frequency

Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.


Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	14 W
Mechanical and Housing	
Overall length	605 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class II
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCH129 1xTL5-14W/840 HF
Full product name	TCH129 1xTL5-14W/840 HF
Full product code	871155900873899
Order code	910502545818
Material Nr. (12NC)	910502545818
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559008738
Numerator - Packs per outer box	16
EAN/UPC - Case	8711559804576

Pentura Mini CC

Dimensional drawing



Product	A
TCH129 1xTL5-14W/840 HF	605 mm

