



# Pentura Mini CC

## TCH129 1xTL5-21W/840 HF

1, TL5, 21 W, 840 neutral white, Electronic high-frequency

Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.


### Product data

<b>General Information</b>	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
<b>Light Technical</b>	
Number of light sources	1
Light source color	840 neutral white
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Power Consumption	21 W
<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class II
<b>Application Conditions</b>	
Suitable for random switching	Not applicable
<b>Product Data</b>	
Order product name	TCH129 1xTL5-21W/840 HF
Full product name	TCH129 1xTL5-21W/840 HF
Full product code	871155900875299
Order code	910502546618
Material Nr. (12NC)	910502546618
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559008752
Numerator - Packs per outer box	16
EAN/UPC - Case	8711559804651

Pentura Mini CC

Dimensional drawing



Product	A
TCH129 1xTL5-21W/840 HF	905 mm

