



Pentura Mini CC

TCH129 1xTL5-28W/840 HF

1 pc - TL5 - 28 W - 840 neutral white - Electronic high-frequency

Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	TL5 [TL5]
Lamp power	28 W
Light source colour	840 neutral white
Kombipack	Lamp(s) included
Gear	HF [Electronic high-frequency]
Protection class IEC	Safety class II (II)
Ready-to-install	Ready-to-install
Glow-wire test	850/5 [Temperature 850 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark

Operating and Electrical	
Input voltage	220 to 240 V


Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Application Conditions	
Suitable for random switching	Not applicable

Product Data	
Full product code	871155900877699
Order product name	TCH129 1xTL5-28W/840 HF
EAN/UPC – product	8711559008776
Order code	00877699
Numerator – quantity per pack	1
Numerator – packs per outer box	16
Material no. (12NC)	910502546818
Net weight (piece)	0.625 kg

Pentura Mini CC

Dimensional drawing



Pentura Mini TCH128

