



Tempo 3 RVP351

RVP351 HPI-TP250W K IC S

MASTER HPI-T Plus, 250 W, Symmetrical

Tempo is a complete floodlighting range offering a wide choice of lamp types and symmetrical and asymmetrical reflectors. It is ideally suited to a variety of outdoor applications – from architectural, facade and billboard lighting to area and (recreational) sports lighting. Besides the Tempo 1, 2 and 3 versions, the range features the high-power Tempo 4, which is available with a variety of light sources up to 2000 W and features an external gear unit. Designed for medium to large-scale floodlighting of sports facilities and similar areas, it is available in single or double-lamp versions and with a choice of narrow or wide-beam optics. The Tempo series' compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. Access to the lamp and gear is quick and easy, via the hinged front glass with its quick-release stainless-steel clips. All Tempo luminaires are RoHS-compliant.

Product data

General Information	
Lamp family code	HPI-TP [MASTER HPI-T Plus]
Gear	CONV [Conventional]
CE mark	Yes
Warranty period	1 years
ENEC mark	-
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Upwards light output ratio	0
Correlated Colour Temperature	4500 K

Colour rendering index (CRI)	65
Light source colour	645 neutral white
Optical cover type	Flat glass
Optic type outdoor	Symmetrical
Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Initial CLO power consumption	{NO} - W
End CLO power consumption	{NO} - W
Power Consumption	250 W
Power Factor (Fraction)	0.85

Tempo 3 RVP351

Connection	Screw connection block 3-pole
Cable	-
Temperature	
Ambient temperature range	-25 to +35 °C
Controls and Dimming	
Dimmable	No
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium die cast
Reflector material	Aluminium
Optic material	Aluminium
Optical cover/lens material	Glass
Fixation material	Steel
Housing Colour	Grey
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	428 mm
Overall width	464 mm
Overall height	146 mm

Effective projected area	0.165 m ²
Dimensions (height x width x depth)	146 x 464 x 428 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Product Data

Order product name	RVP351 HPI-TP250W K IC S
Full product name	RVP351 HPI-TP250W K IC S
Full EOC	871155914971400
Order code	14971400
Material no. (12 NC)	910502548518
Local order code	RVP351H250SK
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711559149714
Numerator – packs per outer box	1
EAN/UPC - Case	8711559149714

Dimensional drawing

