



TTX400 TL-D, GMX440-470 aluminum reflectors

GMX466 258 M-WB

TTX400 REFLECTOR, 2, 58 W

Aluminum one-piece reflectors in hammered, matt and glossy versions. Specially designed for applications where a wide beam, narrow beam, very narrow beam or ultra narrow beam is demanded, e.g. distribution centres and warehouses. Installation via a simple click-in action to the electrical units TMX400. The high efficiencies of these reflectors ensure a highly cost effective solution. Reflector overlapping and mechanical clips delivered with the reflectors enable a proper alignment in case of continuous lines.


Product data

General Information	
Product family code	GMX466 [TTX400 REFLECTOR]
Light Technical	
Number of light sources	2
Operating and Electrical	
Power Consumption	58 W
Mechanical and Housing	
Overall length	1,533 mm

Product Data	
Order product name	GMX466 258 M-WB
Full product name	GMX466 258 M-WB
Full product code	871155968727899
Order code	910502767618
Material Nr. (12NC)	910502767618
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559687278
Numerator - Packs per outer box	5
EAN/UPC - Case	8711559687285

TTX400 TL-D, GMX440-470 aluminum reflectors

Dimensional drawing



Product
GMX466 258 M-WB

