



Impala TBS162

TBS162 4xTL-D18W HFS C6-1000 PI

IMPALA, 4, MASTER TL-D, 18 W, HF Standard, High-gloss optic double parabolic, limit 1000 cd, Push-in connector 3-pole

Impala TBS162 is a functional recessed luminaire for 3 or 4 TL-D 18 W or TL5 14 W fluorescent lamps. It offers a choice of three New Generation optics as well as a prismatic plate. The optics/plate are fitted to the housing by means of an innovative clip for easy installation and maintenance. A smart external connection system enables the mains connection to be made without opening the luminaire. The luminaire fits in visible profile ceilings as standard and, using accessories, in concealed ceilings.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Product family code	TBS162 [IMPALA]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 960 °C, duration 5 s
Light Technical	
Number of light sources	4
Optic type	High-gloss optic double parabolic, limit 1000 cd
Operating and Electrical	
Power Consumption	18 W

Connection	Push-in connector 3-pole
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBS162 4xTL-D18W HFS C6-1000 PI
Full product name	TBS162 4xTL-D18W HFS C6-1000 PI
Full product code	871155969485600
Order code	910502791318
Material Nr. (12NC)	910502791318
Numerator - Quantity Per Pack	1

Impala TBS162

EAN/UPC - Product/Case	8711559694856
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559694856

Dimensional drawing

