



LuxSpace Mini, recessed

DN560B LED12S/830 PSU-E WR WH

LuxSpace2 Mini Low height recessed, LED module, system flux 1200 lm, 830 warm white, Power supply unit DC compatible, external, White reflector without louver, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is.

Product data

General Information	
Lamp family code	LED12S [LED module, system flux 1200 lm]
Cap-Base	- [-]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value.

Service tag	Yes
Product family code	DN560B [LuxSpace2 Mini Low height
	recessed]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	No


Datasheet, 2023, September 5 data subject to change


LuxSpace Mini, recessed

Light Technical	
Luminous Flux	1,150 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	99 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optic type	White reflector without louver
Optical cover type	-
Luminaire light beam spread	80°
Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Consumption	11.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type	32
В	
Temperature	
Ambient temperature range	+10 to +25 ℃
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit DC compatible, external
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel

Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall height	72 mm
Overall diameter	164 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IKO2 [0.2 J standard]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant	:)
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Comp	oliant)
Control gear failure rate at median usefu	ıl 5%
life 50000 h	
Lumen maintenance at median useful	L90
life* 50000 h	
Application Conditions	
Performance ambient temperature Tq	25 ℃
Suitable for random switching	Yes
Product Data	
Order product name	DN560B LED12S/830 PSU-E WR WH
Full product name	DN560B LED12S/830 PSU-E WR WH
Full product code	871829193635000
Order code	910503586414
Material Nr. (12NC)	910503586414
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291936350
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291936350

Dimensional drawing





LuxSpace Mini, recessed



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.