



# LuxSpace Mini, recessed

## DN561B LED12S/830 PSE-E F PG WH

LuxSpace2 Mini Deep recessed - LED Module, system flux 1200 lm - 830 warm white - Power supply unit DC-compatible, external - Facetted reflector - Protection glass - White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Product data

General Information		Optic type	Facetted reflector
Number of light sources	1 pc	Optical cover/lens type	Protection glass
Lamp family code	LED12S [ LED Module, system flux 1200 lm]	Luminaire light beam spread	75°
Light source color	830 warm white	Emergency lighting	-
Cap-Base	- [ - ]	Connection	Push-in connector and pull relief
Light source replaceable	No	Cable	-
Number of gear units	1 unit	Protection class IEC	Safety class II
Gear	-	Glow-wire test	Temperature 850 °C, duration 5 s
Driver/power unit/transformer	Power supply unit DC-compatible, external	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes		

## LuxSpace Mini, recessed

CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Decorative accessories	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	32
RoHS mark	-
Product family code	DN561B [ LuxSpace2 Mini Deep recessed]
Unified glare rating CEN	19

### Light Technical

Optical cover/lens type accessory	Protection glass
-----------------------------------	------------------

### Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.24 ms
Power Factor (Min)	0.9

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Housing configuration	-
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	86 mm

Overall diameter	164 mm
Color	White RAL 9003

### Approval and Application

Ingress protection code	IP20/54 [ Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [ 0.2 J standard]

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1100 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	95 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.43, 0.40) SDCM <3
Initial input power	11.6 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

### Application Conditions


Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

### Product Data

Full product code	871829193688600
Order product name	DN561B LED12S/830 PSE-E F PG WH
EAN/UPC - Product	8718291936886
Order code	910503586467
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503586467
Net Weight (Piece)	0.861 kg

## LuxSpace Mini, recessed

### Dimensional drawing



LuxSpace gen2 Mini DN560B-DN561C

