



# LuxSpace, recessed

## DN570B LED20S/830 PSD-VLC-E F PG WH

LUXSPACE 2 COMPACT LOW HEIGHT, LED Module, system flux 2000 lm, 830 warm white, Power supply unit with DALI interface, DC compatible, external, Facetted reflector, Protection glass, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]	B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Cap-Base	- [-]	Product family code	DN570B [LUXSPACE 2 COMPACT LOW HEIGHT]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Specification
Gear	-	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	No

## LuxSpace, recessed

<b>Light Technical</b>	
Luminous Flux	2,100 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	111 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optic type	Facetted reflector
Optical cover type	Protection glass
Luminaire light beam spread	80°
Unified glare rating CEN	22

<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	19 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

<b>Temperature</b>	
Ambient temperature range	+10 to +25 °C

<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White RAL 9003

Optical cover finish	Frosted
Overall height	96.5 mm
Overall diameter	214 mm

<b>Approval and Application</b>	
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

<b>Product Data</b>	
Order product name	DN570B LED20S/830 PSD-VLC-E F PG WH
Full product name	DN570B LED20S/830 PSD-VLC-E F PG WH
Full product code	871829193079200
Order code	93079200
Material Nr. (12NC)	910503590315
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291930792
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291930792

LuxSpace, recessed

Dimensional drawing

