



# LuxSpace, recessed

## DN571B LED20S/840 PSD-VLC-E C WH

LUXSPACE 2 COMPACT DEEP, LED Module, system flux 2000 lm, 840 neutral white, Power supply unit with DALI interface, DC compatible, external, High-gloss mirror, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Product data

General Information			
Lamp family code	LED20S [LED Module, system flux 2000 lm]	Product family code	DN571B [LUXSPACE 2 COMPACT DEEP]
Cap-Base	- [-]	Lighting Technology	LED
Light source replaceable	No	Value ladder	Specification
Number of gear units	1 unit	CE mark	Yes
Gear	-	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	No
		Light Technical	
		Luminous Flux	2,100 lm
		Correlated Color Temperature (Nom)	4000 K

## LuxSpace, recessed

Luminous Efficacy (rated) (Nom)	121 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	840 neutral white
Optic type	High-gloss mirror
Optical cover type	-
Luminaire light beam spread	70°
Unified glare rating CEN	19

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	17.4 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +25 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White RAL 9003
Optical cover finish	Frosted

Overall height	119 mm
Overall diameter	214 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.37) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life* 50000 h	5 %
Lumen maintenance at median useful life* L90 50000 h	
Lumen maintenance at median useful life* L80 100000 h	

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	DN571B LED20S/840 PSD-VLC-E C WH
Full product name	DN571B LED20S/840 PSD-VLC-E C WH
Full product code	871829193120100
Order code	93120100
Material Nr. (12NC)	910503594415
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291931201
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291931201

## LuxSpace, recessed

### Dimensional drawing

