



# LuxSpace, recessed

## DN571B LED20S/830 PSED-VLC-E WR WH

LUXSPACE 2 COMPACT DEEP - LED Module, system flux 2000 lm - 830 warm white - Power supply unit with DALI interface external, DC compatible for central emergency lighting - White reflector without louver - White

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Product data

General Information	
Number of light sources	1 [ 1 pc]
Lamp family code	LED20S [ LED Module, system flux 2000 lm]
Light source colour	830 warm white
Cap base	- [ -]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver/power unit/transformer	PSED-E [ Power supply unit with DALI interface external, DC compatible for central emergency lighting]
Driver included	Yes
Optic type	WR [ White reflector without louver]

Optical cover/lens type	No [ -]
Luminaire light beam spread	70°
Emergency lighting	No [ -]
Control interface	DALI
Connection	Push-in connector and pull relief
Cable	-
Protection class IEC	Safety class II
Glow-wire test	Temperature 850 °C, duration 5 s
Flammability mark	F [ For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	No

## LuxSpace, recessed

Warranty period	5 years
Decorative accessories	No [-]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB	24
RoHS mark	-
Product Family Code	DN571B [ LUXSPACE 2 COMPACT DEEP]
Unified glare rating CEN	25

### Light Technical

Optical cover/lens type accessory	No [-]
-----------------------------------	--------

### Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	20.4 A
Inrush time	0.195 ms
Power factor (min.)	0.9

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing configuration	BV [ Basic version]
Housing material	Aluminium die-cast
Reflector material	Polycarbonate aluminium coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	119 mm
Overall diameter	214 mm

Colour	White
--------	-------

### Approval and Application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

### Initial Performance (IEC Compliant)

Initial luminous flux	2000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	105 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	>80
Initial chromaticity	(0.43, 0.40) SDCM <3
Initial input power	19 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

### Application Conditions


Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%

### Product Data

Full product code	871829193128700
Order product name	DN571B LED20S/830 PSED-VLC-E WR WH
EAN/UPC – product	8718291931287
Order code	93128700
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910503595215
Net weight (piece)	1.080 kg

# LuxSpace, recessed


## Dimensional drawing




### LuxSpace gen2 DN570B-DN572B

## Photometric data

DN571B PSED-E 1xLED20S/830 WR



DN571B PSED-E 1xLED20S/830 WR



### IFGU1\_DN571B PSED-E 1xLED20S830 WR.EPS

### IFPC1\_DN571B PSED-E 1xLED20S830 WR.EPS

