



LuxSpace, recessed

DN571B LED20S/830 PSU-E C PG WH

LUXSPACE 2 COMPACT DEEP, LED Module, system flux 2000 lm, 830 warm white, Power supply unit DC compatible, external, High-gloss mirror, Protection glass, White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is. For office applications LuxSpace supports health and wellbeing having dedicated Tunable White products and lighting controls.

Product data

| General Information | | | |
|--------------------------|--|------------------------------------|---|
| Lamp family code | LED20S [LED Module, system flux 2000 lm] | Product family code | DN571B [LUXSPACE 2 COMPACT DEEP] |
| Cap-Base | - [-] | Lighting Technology | LED |
| Light source replaceable | No | Value ladder | Specification |
| Number of gear units | 1 unit | CE mark | Yes |
| Gear | - | Warranty period | 5 years |
| Driver included | Yes | Flammability mark | For mounting on normally flammable surfaces |
| Remarks | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | ENEC mark | ENEC mark |
| | | Glow-wire test | Temperature 850 °C, duration 5 s |
| | | EU RoHS compliant | No |
| | | Light Technical | |
| | | Luminous Flux | 2,000 lm |
| | | Correlated Color Temperature (Nom) | 3000 K |

LuxSpace, recessed

| | |
|---------------------------------|-------------------|
| Luminous Efficacy (rated) (Nom) | 105 lm/W |
| Color rendering index (CRI) | >80 |
| Number of light sources | 1 |
| Light source color | 830 warm white |
| Optic type | High-gloss mirror |
| Optical cover type | Protection glass |
| Luminaire light beam spread | 70° |
| Unified glare rating CEN | 19 |

Operating and Electrical

| | |
|--|-----------------------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 18 A |
| Inrush time | 0.24 ms |
| Power Consumption | 19 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Push-in connector and pull relief |
| Cable | - |
| Number of products on MCB of 16 A type B | 32 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | +10 to +25 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|---|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit DC compatible, external |
| Constant light output | No |

Mechanical and Housing

| | |
|------------------------|-------------------------------|
| Housing Material | Aluminum die cast |
| Reflector material | Polycarbonate aluminum coated |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material | Steel |
| Housing Color | White RAL 9003 |
| Optical cover finish | Frosted |
| Overall height | 119 mm |

| | |
|------------------|--------|
| Overall diameter | 214 mm |
|------------------|--------|

Approval and Application

| | |
|------------------------------|---|
| Ingress protection code | IP20/54 [Finger-protected; dust accumulation-protected, splash-proof] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Protection class IEC | Safety class II |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|---------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.43, 0.40) SDCM≤2 |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---|-----|
| Control gear failure rate at median useful life 50000 h | 5 % |
| Lumen maintenance at median useful life* 50000 h | L90 |
| Lumen maintenance at median useful life* 100000 h | L80 |


Application Conditions

| | |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
| Suitable for random switching | Yes |

Product Data

| | |
|---------------------------------|---------------------------------|
| Order product name | DN571B LED20S/830 PSU-E C PG WH |
| Full product name | DN571B LED20S/830 PSU-E C PG WH |
| Full product code | 871829193141600 |
| Order code | 910503596515 |
| Material Nr. (12NC) | 910503596515 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291931416 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8718291931416 |

Dimensional drawing



LuxSpace, recessed

