



# LuxSpace, recessed

## DN571B LED20S/830 PSED-VLC-E C PG WH

LUXSPACE 2 COMPACT DEEP - LED Module, system flux 2000 lm - 830 warm white - Power supply unit with DALI interface, DC-compatible, external - High-gloss mirror - Protection glass - White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application. For office applications LuxSpace supports the general feeling of health and wellbeing having dedicated Tunable White products

### Product data

General Information	
Number of light sources	1 pc
Lamp family code	LED20S [ LED Module, system flux 2000 lm]
Light source color	830 warm white
Cap-Base	- [ -]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver/power unit/transformer	Power supply unit with DALI interface, DC-compatible, external
Driver included	Yes

Optic type	High-gloss mirror
Optical cover/lens type	Protection glass
Luminaire light beam spread	70°
Emergency lighting	-
Control interface	DALI
Connection	Push-in connector and pull relief
Cable	-
Protection class IEC	Safety class II
Glow-wire test	Temperature 850 °C, duration 5 s
Flammability mark	For mounting on normally flammable surfaces

## LuxSpace, recessed

CE mark	CE mark
ENEC mark	ENEC mark
UL mark	-
Warranty period	5 years
Decorative accessories	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	24
RoHS mark	-
Product family code	DN571B [ LUXSPACE 2 COMPACT DEEP ]
Unified glare rating CEN	19

### Light Technical

Optical cover/lens type accessory	Protection glass
-----------------------------------	------------------

### Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	20.4 A
Inrush time	0.195 ms
Power Factor (Min)	0.9

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing configuration	Basic version
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	119 mm

Overall diameter	214 mm
Color	White RAL 9003

### Approval and Application

Ingress protection code	IP20/54 [ Finger-protected; dust accumulation-protected, splash-proof ]
Mech. impact protection code	IK02 [ 0.2 J standard ]

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	2000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	105 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.43, 0.40) SDCM <3
Initial input power	19 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

### Application Conditions


Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Full product code	871829193142300
Order product name	DN571B LED20S/830 PSED-VLC-E C PG WH
EAN/UPC - Product	8718291931423
Order code	910503596615
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503596615
Net Weight (Piece)	1.246 kg

# LuxSpace, recessed


## Dimensional drawing




## LuxSpace gen2 DN570B-DN572B

## Photometric data

DN571B PSED-E 1xLED20S/830 C PG



DN571B PSED-E 1xLED20S/830 C PG



## IFGU1\_DN571B PSED-E 1xLED20S830 C PG.EPS

## IFPC1\_DN571B PSED-E 1xLED20S830 C PG.EPS

