



TBS165

TBS165 G 2xTL5-28W/840 HFS C6 PIP SC

2, TL5, 28 W, 840 neutral white, HF Standard, High-gloss optic double parabolic closed, Push-in connector and pull relief

Designed to address the need for energy-efficient basic lighting, the TBS165 luminaire makes it possible to save energy by replacing outdated electromagnetic installations with Philips TL5 technology. Featuring innovative dedicated TL5 optics, a choice of ballasts, sensors (presence detection, daylight regulation) and emergency lighting, the TBS165 range can be used for general lighting in a wide variety of applications, including offices, corridors, schools and shops (supermarkets, DIY). Combining high-frequency gear, sensors and MASTER TL5 lamps, it allows substantial energy savings. The low-height recessed luminaire fits in exposed ceilings. Conveniently, it does not have to be opened, as it has pre-installed lamps and can be connected from the outside.

Product data

General Information		Operating and Electrical	
Lamp family code	TL5 [TL5]	Input Voltage	220 to 240 V
Gear	HFS [HF Standard]	Power Consumption	28 W
CE mark	Yes	Connection	Push-in connector and pull relief
Flammability mark	For mounting on normally flammable surfaces	Approval and Application	
Glow-wire test	Temperature 850 °C, duration 5 s	Ingress protection code	IP20 [Finger-protected]
Light Technical		Mech. impact protection code	IK02 [0.2 J standard]
Number of light sources	2	Protection class IEC	Safety class I
Light source color	840 neutral white	Application Conditions	
Optic type	High-gloss optic double parabolic closed	Suitable for random switching	Not applicable

TBS165

Product Data	
Order product name	TBS165 G 2xTL5-28W/840 HFS C6 PIP SC
Full product name	TBS165 G 2xTL5-28W/840 HFS C6 PIP SC
Full product code	871794388814600
Order code	910503653018
Material Nr. (12NC)	910503653018

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943888146
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943888146

Dimensional drawing

