



Gondola

FWG251 2xPL-C/4P26W HF GR

Gondola, 2, MASTER PL-C 4 Pin, 26 W, Electronic high-frequency, Grey

Gondola is a waterproof and shock- and vandal-resistant luminaire with a fresh, appealing design. Its highly efficient HF driver significantly reduces energy consumption, while the long lifetime of the light source means that maintenance costs are kept to a minimum. Gondola can be wall- or ceiling-mounted and is ideal for efficient illumination of areas such as stairwells and corridors.

Product data

General Information		Mechanical and Housing	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]	Housing Color	Grey
Cap-Base	G24Q-3 [G24q-3]		
Gear	HF [Electronic high-frequency]	Approval and Application	
Product family code	FWG251 [Gondola]	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
CE mark	Yes	Mech. impact protection code	IK10 [20 J vandal-resistant]
Flammability mark	For mounting on normally flammable surfaces	Protection class IEC	Safety class I
ENEC mark	ENEC mark	Application Conditions	
Glow-wire test	Temperature 850 °C, duration 5 s	Suitable for random switching	Not applicable
Light Technical		Product Data	
Number of light sources	2	Order product name	FWG251 2xPL-C/4P26W HF GR
Operating and Electrical		Full product name	FWG251 2xPL-C/4P26W HF GR
Input Voltage	220 to 240 V	Full product code	871794389224299
Power Consumption	26 W	Order code	910503668618
		Material Nr. (12NC)	910503668618
		Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8717943892242
Numerator - Packs per outer box	4
EAN/UPC - Case	8717943892587

Dimensional drawing

