



# TBS165

## TBS165 G 4xTL5-14W/840 HF C3 PIP SC FR

4, TL5, 14 W, 840 neutral white, HF Performer, High-gloss mirror matt aluminum louver, Push-in connector and pull relief

Designed to address the need for energy-efficient basic lighting, the TBS165 luminaire makes it possible to save energy by replacing outdated electromagnetic installations with Philips TL5 technology. Featuring innovative dedicated TL5 optics, a choice of ballasts, sensors (presence detection, daylight regulation) and emergency lighting, the TBS165 range can be used for general lighting in a wide variety of applications, including offices, corridors, schools and shops (supermarkets, DIY). Combining high-frequency gear, sensors and MASTER TL5 lamps, it allows substantial energy savings. The low-height recessed luminaire fits in exposed ceilings. Conveniently, it does not have to be opened, as it has pre-installed lamps and can be connected from the outside.

### Product data

General Information		Operating and Electrical	
Lamp family code	TL5 [TL5]	Input Voltage	220 to 240 V
Gear	HFP [HF Performer]	Power Consumption	14 W
CE mark	Yes	Connection	Push-in connector and pull relief
Flammability mark	For mounting on normally flammable surfaces	Approval and Application	
Glow-wire test	Temperature 850 °C, duration 5 s	Ingress protection code	IP20 [Finger-protected]
Light Technical		Mech. impact protection code	IK02 [0.2 J standard]
Number of light sources	4	Protection class IEC	Safety class I
Light source color	840 neutral white	Application Conditions	
Optic type	High-gloss mirror matt aluminum louver	Suitable for random switching	Not applicable

TBS165

Product Data	
Order product name	TBS165 G 4xTL5-14W/840 HF C3 PIP SC FR
Full product name	TBS165 G 4xTL5-14W/840 HF C3 PIP SC FR
Full product code	871794389419200
Order code	910503678918
Material Nr. (12NC)	910503678918

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943894192
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943894192

Dimensional drawing

