



C-Splash 2

C-Splash 2, 22° Frosted Lens

C-Splash 2, 22° Frosted Lens

C-Splash 2 is an ultra-thin, submersible fixture designed to provide vibrant colour and colour-changing light in fresh and saltwater locations to a depth of 4.6 meters. With its watertight cast brass housing and silicon bronze adjusting hardware, C-Splash 2 is perfect for water-based applications such as fountains and theme park installations, as well as for applications situated in harsh environments.

Product data

General information	
Number of light sources	18 [18 pcs]
Lamp family code	LED-HB [LED High Brightness]
Lamp colour code	Red, green and blue
Light source replaceable	No
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Luminaire light beam spread	22°
Protection class IEC	Safety class III (III)
CE mark	CE mark
Lifetime to 50% luminous flux	50000 h
Optic type outdoor	Medium beam angle 22°
Operating and electrical	
Input Voltage	24 V
Input frequency	0 Hz
Controls and dimming	
Dimmable	No

Mechanical and housing	
Colour	Brass
Approval and application	
Ingress protection code	IP68 [Dust penetration-protected, pressure watertight]
Energy Efficiency Class	G
	942284
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	515 lm
Initial LED luminaire efficacy	23.3 lm/W
Initial input power	31.3 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 50 °C	50000
Reported	


C-Splash 2

Application conditions	
Ambient temperature range	-40 to +50 °C
Product data	
Full product code	871794370184100
Order product name	BCP468 18xLED-HB/RGB 24V IP68 22 BRS
EAN/UPC – product	8717943701841
Order code	116-000024-00
SAP numerator – quantity per pack	1

Local code description	LUMINARIA LED BRP392LED156NW130W220DM
Numerator – packs per outer box	1
SAP material	910503700616
Net Weight (Piece)	10.000 kg
Commercial Code	116-000024-00
Commercial Code	C-Splash 2, 22° Frosted Lens



Dimensional drawing



BCP468 18xLED-HB/RGB 24V IP68 22 BRS

