



# C-Splash 2



## C-Splash 2, 10° Clear Lens

### C-Splash 2, 10° Clear Lens

C-Splash 2 is an ultra-thin, submersible luminaire designed to provide vibrant color and color-changing light in water to a depth of 4.6 m (15 ft). With its watertight cast brass housing and silicon bronze adjusting hardware, C-Splash 2 is perfect for water-based applications such as fountains and theme park installations, as well as for applications situated in harsh environments.

#### Product data

General information	
Number of light sources	18 pcs
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Red, green and blue
Light source replaceable	No
Driver/power unit/transformer	Power supply unit
Driver included	Yes
Luminaire light beam spread	10°
Protection class IEC	Safety class III
CE mark	CE mark
Lifetime to 50% luminous flux	50000 h
Optic type outdoor	Narrow beam angle 10°
Operating and electrical	
Input Voltage	24 V
Input Frequency	0 Hz
Controls and dimming	
Dimmable	No

Mechanical and housing	
Color	Brass
Approval and application	
Ingress protection code	IP68 [ Dust penetration-protected, pressure watertight]
Energy Efficiency Class	G
EPREL Registration Number	942285
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	583 lm
Initial LED luminaire efficacy	23.3 lm/W
Initial input power	31.3 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 50°C Reported	50000
Application conditions	
Ambient temperature range	-40 to +50 °C


C-Splash 2

Product data	
Full product code	871794370185800
Order product name	BCP468 18xLED-HB/RGB 24V IP68 10 BRS
EAN/UPC - Product	8717943701858
Order code	116-000024-01
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Material Nr. (12NC)	910503700617
Net Weight (Piece)	10.000 kg
Catalog Number	116-000024-01
Catalog Number Description	C-Splash 2, 10° Clear Lens

IP 68

Dimensional drawing



BCP468 18xLED-HB/RGB 24V IP68 10 BRS

