



ColorBurst 6

ColorBurst 6 BCP466 18xLED-HB/RGB 24V 22 WH

Red, green and blue - Medium beam angle 22° - White

ColorBurst 6 combines the classical look of a round spotlight with all the benefits of intelligent LED technology. Enclosed in a rugged, die-cast aluminum housing, this compact spotlighting and wall-washing fixture projects rich, saturated colors and color-changing effects, both indoors and outdoors. Enclosed wiring gives ColorBurst 6 a neat appearance and optimum positioning. The housing is equipped with a three-screw accessory ring to affix spread lenses, egg-crate louvers, and other attachments.

Product data

General Information	
Number of light sources	18 [18 pcs]
Lamp family code	LED-HB [LED High Brightness]
Light source colour	Red, green and blue
Light source replaceable	No
Driver included	Yes
Luminaire light beam spread	22°
Connection	No [-]
Protection class IEC	Safety class I (I)
CE mark	CE mark
UL mark	UL and cUL mark
Lifetime to 70% luminous flux	70000 h
Outdoor optic type	Medium beam angle 22°
Operating and Electrical	
Input voltage	24 V
Input frequency	0 Hz

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Colour	White
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Initial Performance (IEC Compliant)	
Initial input power	31.3 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 50°C Reported	50000

ColorBurst 6

Application Conditions

Ambient temperature range -20 to +50 °C

Product Data

Full product code 871794370223799
Order product name ColorBurst 6 BCP466 18xLED-HB/RGB 24V
22 WH
EAN/UPC – product 8717943702237

Order code 70223799


Numerator – quantity per pack 1

Numerator – packs per outer box 4


Material no. (12NC) 910503700733

Net weight (piece) 1.450 kg

Dimensional drawing



ColorBurst 6



ColorBurst 6

