



ColorBurst 6

ColorBurst 6 BCP466 18xLED-HB/RGB 24V 12 BK

Red, green and blue - Narrow beam angle 12° - Black

ColorBurst 6 combines the classical look of a round, 152 mm (6 in) spotlight with all the benefits of intelligent LED technology. Enclosed in a rugged, die-cast aluminium housing, this compact spotlighting and wall-washing luminaire projects rich, saturated colors and color-changing effects both indoors and outdoors. Enclosed wiring gives ColorBurst 6 a neat appearance and optimum positioning. The housing is equipped with a three-screw accessory ring to affix spread lenses, egg crate louvers, and other attachments.

Product data

General Information	
Number of light sources	18 pcs
Lamp family code	LED-HB [LED High Brightness]
Light source color	Red, green and blue
Light source replaceable	No
Driver included	Yes
Luminaire light beam spread	10°
Connection	-
Protection class IEC	Safety class I
CE mark	CE mark
UL mark	UL and cUL mark
Lifetime to 70% luminous flux	70000 h
Optic type outdoor	Narrow beam angle 12°
Operating and Electrical	
Input Voltage	24 V
Input Frequency	0 Hz

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Color	Black
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Initial Performance (IEC Compliant)	
Initial input power	31.3 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 50°C Reported	50000

ColorBurst 6

Application Conditions

Ambient temperature range -20 to +50 °C

Product Data

Full product code	871794370226899
Order product name	ColorBurst 6 BCP466 18xLED-HB/RGB 24V 12 BK
EAN/UPC - Product	8717943702268

Order code 910503700736


Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 4


Material Nr. (12NC) 910503700736

Net Weight (Piece) 1.450 kg

Dimensional drawing



ColorBurst 6



ColorBurst 6

