



# eW Cove MX Powercore Precision Dimming

**eW Cove MX Powercore, 4000 K, 50° x 70° Beam Angle, 12.5 W/ft, 305 mm (1 ft)**

eW Cove MX Powercore, 4000 K, 50° x 70° Beam Angle, 12.5 W/ft, 305 mm (1 ft)

With its superior light output, wide beam angle, and range of fixed colours and colour temperatures, eW Cove MX Powercore Precision Dimming can be used for accent lighting and indirect general illumination, as well as the full range of wall and ceiling cove applications. This fixture meets or exceeds the performance of comparable linear fluorescent strip cove lights while lowering installation, energy, and maintenance costs. eW Cove MX Powercore Precision Dimming offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light. Integrated Powercore technology ensures rapid, efficient and accurate control of power output to the fixture directly from line voltage, eliminating the need for external power supplies.

## Product data

General information			
Number of light sources	10 [ 10 pcs]	Optic type	MB [ Medium beam]
Lamp family code	LED-HB [ LED High Brightness]	Optical cover/lens type	PC [ Polycarbonate bowl/cover]
Lamp colour code	Neutral white	Luminaire light beam spread	50° x 70°
Light source replaceable	No	Protection class IEC	Safety class I (I)
Driver/power unit/transformer	PSR [ Power supply unit regulating]	Ready-to-install	Ready-to-install
Driver included	Yes	Type description	No
		CE mark	CE mark


eW Cove MX Powercore Precision Dimming

UL mark	UL and cUL mark
CCC mark	CCC mark
Operating and electrical	
Input Voltage	100 to 277 V
Input frequency	50 to 60 Hz
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Aluminum die-cast
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	305 mm
Colour	White
Approval and application	
Ingress protection code	IP20 [ Finger-protected]
FCC mark	FCC Class B
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	518 lm
Initial luminous flux at colour temperature of 4,000 K	518 lm
Initial LED luminaire efficacy	43.5 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	83
Initial input power	12.5 W

Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	65000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	65000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	65000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	65000
Application conditions	
Ambient temperature range	-20 to +50 °C
Maximum dimming level	10% (depends on dimmer, ELV)
Suitable for random switching	Yes
Product data	
Full product code	871794379667099
Order product name	BCX416 10xLED-HB-4000 100-277V MB
EAN/UPC – product	8717943796670
Order code	523-000050-13
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	910503700991
Net Weight (Piece)	0.460 kg
Commercial Code	523-000050-13
Commercial Code	eW Cove MX Powercore, 4000 K, 50° x 70° Beam Angle, 12.5 W/ft, 305 mm (1 ft)



Dimensional drawing



BCX416 10xLED-HB-4000 100-277V MB

## eW Cove MX Powercore Precision Dimming

