



eW Cove MX Powercore

eW Cove MX Powercore, 2700 K, 125° x 120° Beam Angle, 12.5 W/ft, 305 mm (1 ft)

eW Cove MX Powercore, 2700 K, 125° x 120° Beam Angle, 12.5 W/ft, 305 mm (1 ft)

With its superior light output, wide beam angle, and range of fixed colors and color temperatures, eW Cove MX Powercore can be used for accent lighting and indirect general illumination, as well as the full range of wall and ceiling cove applications. This fixture meets or exceeds the performance of comparable linear fluorescent strip cove lights while lowering installation, energy, and maintenance costs. eW Cove MX Powercore offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light. Integrated Powercore technology ensures rapid, efficient and accurate control of power output to the fixture directly from line voltage, eliminating the need for external power supplies. Use of standard wiring dramatically simplifies installation and helps lower total system cost.

Product data

General information			
Number of light sources	10 [10 pcs]	Luminaire light beam spread	125° x 120°
Lamp family code	LED-HB [LED High Brightness]	Protection class IEC	Safety class I (I)
Light source color	Warm white	Ready-to-install	Ready-to-install
Light source replaceable	No	Type description	No
Driver/power unit/transformer	PSR [Power supply unit regulating]	CE mark	CE mark
Driver included	Yes	UL mark	UL and cUL mark
Optic type	WB [Wide beam]	CCC mark	CCC mark
Optical cover/lens type	PC [Polycarbonate bowl/cover]		


eW Cove MX Powercore

Operating and electrical	
Input Voltage	100 to 277 V
Input Frequency	50 to 60 Hz
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing Material	Aluminum die-cast
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Length	305 mm
Color	White
Approval and application	
Ingress protection code	IP20 [Finger-protected]
FCC mark	FCC Class B
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	527 lm
Initial luminous flux at color temperature of 2700 K	527 lm
Initial LED luminaire efficacy	43.9 lm/W
Init. Corr. Color Temperature	2700 K
Init. Color Rendering Index	82
Initial input power	12.5 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Calculated	100000

Lumen Maintenance 50% at 25°C Reported	65000
Lumen Maintenance 50% at 50°C Calculated	100000
Lumen Maintenance 50% at 50°C Reported	65000
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	65000
Lumen Maintenance 70% at 50°C Calculated	100000
Lumen Maintenance 70% at 50°C Reported	65000
Application conditions	
Ambient temperature range	-20 to +50 °C
Maximum dim level	10% (depends on dimmer, ELV)
Suitable for random switching	Yes
Product data	
Full product code	871829137625599
Order product name	BCX416 10xLED-HB/2700 100-277V WB
EAN/UPC - Product	8718291376255
Order code	523-000050-17
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	910503701726
Net Weight (Piece)	0.400 kg
Commercial Code	523-000050-17
Commercial Code	eW Cove MX Powercore, 2700 K, 125° x 120° Beam Angle, 12.5 W/ft, 305 mm (1 ft)



Dimensional drawing



BCX416 10xLED-HB/2700 100-277V WB

