



eColor Cove MX Powercore

eColor Cove MX Powercore, Red, 50° x 70° Beam Angle, 1.2 m (4 ft)

eColor Cove MX Powercore, Red, 50° x 70° Beam Angle, 1.2 m (4 ft)

eColor Cove MX Powercore delivers the highest light output in the line of solid colour linear cove lights from Color Kinetics. With medium and wide beam angles and a range of fixed colours, luminaires can be used for accent lighting as well as wall and ceiling cove applications. Offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light.

Product data

General Information		CCC mark	
Number of light sources	10 [10 pcs]	CCC mark	
Lamp family code	LED-HB [LED High Brightness]		
Lamp colour code	Red		
Light source replaceable	No		
Driver/power unit/transformer	PSR [Power supply unit regulating]		
Driver included	Yes		
Optic type	MB [Medium beam]		
Optical cover/lens type	PC [Polycarbonate bowl/cover]		
Luminaire light beam spread	50° x 70°		
Protection class IEC	Safety class I (I)		
Ready-to-install	Ready-to-install		
CE mark	CE mark		
UL mark	UL and cUL mark		
Operating and Electrical			
Input Voltage	100 to 277 V		
Input frequency	50 to 60 Hz		
Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Housing material	Aluminum die-cast		
Optic material	Polycarbonate		
Optical cover/lens material	Polycarbonate		



eColor Cove MX Powercore

Colour	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Initial Performance (IEC Compliant)	
Initial input power	50 W
Application Conditions	
Ambient temperature range	-20 to +50 °C
Maximum dimming level	10% (depends on dimmer, ELV)
Product Data	
Full product code	871829137845799

Order product name	BCX421 10xLED-HB/RD 100-277V L1220 MB
EAN/UPC – product	8718291378457
Order code	223-000050-20
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	910503702595
SAP net weight (piece)	2.050 kg
Commercial Code	223-000050-20
Catalogue number description	eColor Cove MX Powercore, Red, 50° x 70° Beam Angle, 1.2 m (4 ft)



Dimensional drawing



eColor Cove MX Powercore

eColor Cove MX Powercore

