



# eColor Cove MX Powercore

**eColor Cove MX Powercore, Amber, 50° x 70° Beam Angle, 1.2 m (4 ft)**

eColor Cove MX Powercore, Amber, 50° x 70° Beam Angle, 1.2 m (4 ft)

eColor Cove MX Powercore delivers the highest light output in the line of solid colour linear cove lights from Color Kinetics. With medium and wide beam angles and a range of fixed colours, luminaires can be used for accent lighting as well as wall and ceiling cove applications. Offers environmentally conscious buyers a green, energy-efficient lighting solution without sacrificing quality or quantity of light.

## Product data

General Information		CCC mark	
Number of light sources	10 [ 10 pcs]	CCC mark	
Lamp family code	LED-HB [ LED High Brightness]		
Light source colour	Amber	Operating and Electrical	
Light source replaceable	No	Input Voltage	100 to 277 V
Driver/power unit/transformer	PSR [ Power supply unit regulating]	Input frequency	50 to 60 Hz
Driver included	Yes	Controls and Dimming	
Optic type	MB [ Medium beam]	Dimmable	Yes
Optical cover/lens type	PC [ Polycarbonate bowl/cover]	Mechanical and Housing	
Luminaire light beam spread	50° x 70°	Housing material	Aluminium die-cast
Protection class IEC	Safety class I	Optic material	Polycarbonate
Ready-to-install	Ready-to-install	Optical cover/lens material	Polycarbonate
CE mark	CE mark		
UL mark	UL and cUL mark		


## eColor Cove MX Powercore

Colour	White
<b>Approval and Application</b>	
Ingress protection code	IP20 [ Finger-protected]
<b>Initial Performance (IEC Compliant)</b>	
Initial input power	40 W
<b>Application Conditions</b>	
Ambient temperature range	-20 to +50 °C
Maximum dimming level	10% (depends on dimmer, ELV)
<b>Product Data</b>	
Full product code	871829137848899

Order product name	BCX421 10xLED-HB/AM 100-277V L1220 MB
EAN/UPC – product	8718291378488
Order code	223-000050-23
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	910503702598
SAP net weight (piece)	2.050 kg
Commercial Code	223-000050-23
Catalogue number description	eColor Cove MX Powercore, Amber, 50° x 70° Beam Angle, 1.2 m (4 ft)



### Dimensional drawing



eColor Cove MX Powercore

