



ColorGraz QLX Powercore

ColorGraz QLX Powercore, RGB, 30° x 60° Beam Angle, 610 mm (2 ft)

ColorGraz QLX Powercore, RGB, 30° x 60° Beam Angle, 610 mm (2 ft)

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze QLX Powercore is capable of illuminating over 10 metres at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General Information		Input frequency	
Lamp family code	LED-HB [LED High Brightness]	50 to 60 Hz	
Light source colour	RGB	Controls and Dimming	
Light source replaceable	No	Dimmable	
Driver included	Yes	Yes	
Luminaire light beam spread	30° x 60°	Mechanical and Housing	
Protection class IEC	Safety class I	Housing material	
CE mark	CE mark	Extruded aluminium	
UL mark	UL and cUL mark	Optic material	
Lifetime to 70% luminous flux	100000 h	Polycarbonate	
Operating and Electrical		Optical cover/lens material	
Input Voltage		Polycarbonate	
		Length	
		609 mm	
		Colour	
		aluminium	

ColorGraz e QLX Powercore

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G

Initial Performance (IEC Compliant)

Initial input power	30 W
---------------------	------

Over Time Performance (IEC Compliant)

Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	100000
Lumen Maintenance 50% at 50 °C Calculated	80000
Lumen Maintenance 50% at 50 °C Reported	80000
Lumen Maintenance 70% at 25 °C Calculated	60000
Lumen Maintenance 70% at 25 °C Reported	100000
Lumen Maintenance 70% at 50 °C Calculated	60000
Lumen Maintenance 70% at 50 °C Reported	91000

Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data


Full product code	871829160411299
Order product name	BCS467 30x60 RGB L609
EAN/UPC – product	8718291604112
Order code	123-000079-28
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503703355
SAP net weight (piece)	2.700 kg
Commercial Code	123-000079-28
Catalogue number description	ColorGraz e QLX Powercore, RGB, 30° x 60° Beam Angle, 610 mm (2 ft)



Dimensional drawing



Graze



Graze

