



eColor Graze MX Powercore

eColor Graze MX Powercore, Green, 15° x 30° Beam Angle, 610 mm (2 ft)

Green - 15° x 30° - 610 mm - Aluminum

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [LED High Brightness]	Dimmable	Yes
Light source colour	Green		
Light source replaceable	No	Mechanical and Housing	
Driver included	Yes	Housing material	Aluminum extruded
Optical cover/lens type	PCC [Polycarbonate bowl/cover clear]	Optic material	Polycarbonate
Luminaire light beam spread	15° x 30°	Optical cover/lens material	Polycarbonate
Protection class IEC	Safety class I (I)	Length	610 mm
CE mark	CE mark	Colour	Aluminum
UL mark	UL and cUL mark	Approval and Application	
Operating and Electrical		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Input Voltage	100 to 277 V	Mech. impact protection code	IK10 [20 J vandal-resistant]
Input frequency	50 to 60 Hz	Vibration standard	Complies with ANSI C136.31, 3G

eColor Graze MX Powercore

Vibration rating	Complies with ANSI C136.31, 3G
Initial Performance (IEC Compliant)	
Initial input power	30 W
Application Conditions	
Ambient temperature range	-40 to +50 °C
Product Data	
Full product code	871829160546199
Order product name	BCS439 15x30 GN L609
EAN/UPC – product	8718291605461

Order code	223-000080-29
SAP numerator – quantity per pack 1	
Numerator – packs per outer box	4
SAP material	910503703419
Net Weight (Piece)	2.700 kg
Commercial Code	223-000080-29
Commercial Code	eColor Graze MX Powercore, Green, 15° x 30° Beam Angle, 610 mm (2 ft)



Dimensional drawing

