



eColor Graze QLX Powercore

**eColor Graze QLX Powercore, Amber, 60° x 30°
Beam Angle, 610 mm (2 ft)**

Amber - 60° x 30° - 609 mm - Aluminium

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze QLX Powercore is capable of illuminating over 10 metres at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General Information		Input frequency	
Lamp family code	LED-HB [LED High Brightness]	50 to 60 Hz	
Light source colour	Amber	Controls and Dimming	
Light source replaceable	No	Dimmable	Yes
Driver included	Yes	Mechanical and Housing	
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]	Housing material	Extruded aluminium
Luminaire light beam spread	60° x 30°	Optic material	Polycarbonate
Protection class IEC	Safety class I	Optical cover/lens material	Polycarbonate
CE mark	CE mark	Length	609 mm
UL mark	UL and cUL mark	Colour	Aluminium
Lifetime to 70% luminous flux	100000 h	Approval and Application	
Operating and Electrical		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Input Voltage	100 to 277 V	Mech. impact protection code	IK10 [20 J vandal-resistant]

eColor Graze QLX Powercore

Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G
Initial Performance (IEC Compliant)	
Initial input power	28 W
Application Conditions	
Ambient temperature range	-40 to +50 °C
Product Data	
Full product code	871829160706999
Order product name	BCS447 60x30 AM L609

EAN/UPC – product	8718291607069
Order code	223-000081-39
SAP numerator – quantity per pack 1	
Numerator – packs per outer box	4
SAP material	910503703509
Net Weight (Piece)	2.700 kg
Commercial Code	223-000081-39
Commercial Code	eColor Graze QLX Powercore, Amber, 60° x 30° Beam Angle, 610 mm (2 ft)



Dimensional drawing

