



# iW Graze QLX Powercore

**iW Graze QLX Powercore, 30° x 60° Beam Angle, 305 mm (1 ft)**

iW Graze QLX Powercore, 30° x 60° Beam Angle, 305 mm (1 ft)

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze QLX Powercore is capable of illuminating over 10 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

## Product data

| General Information           |                               | Controls and Dimming                |   |
|-------------------------------|-------------------------------|-------------------------------------|---|
| Lamp family code              | LED-HB [ LED High Brightness] | Dimmable                            | Yes   |
| Light source replaceable      | No                            |                                     |   |
| Driver included               | Yes                           | Mechanical and Housing              |   |
| Luminaire light beam spread   | 30° x 60°                     | Length                              | 305 mm  |
| Protection class IEC          | Safety class I (I)            |                                     |   |
| CE mark                       | CE mark                       | Approval and Application            |   |
| UL mark                       | UL mark                       | Ingress protection code             | IP66 [ Dust penetration-protected, jet-proof] |
| Lifetime to 70% luminous flux | 100000 h                      | Mech. impact protection code        | IK10 [ 20 J vandal-resistant]                 |
|                               |                               | Vibration standard                  | Complies with ANSI C136.31, 3G                |
|                               |                               | Vibration rating                    | Complies with ANSI C136.31, 3G                |
| Operating and Electrical      |                               |                                     |   |
| Input Voltage                 | 100 to 277 V                  | Initial Performance (IEC Compliant) |   |
| Input frequency               | 50 to 60 Hz                   | Initial input power                 | 15 W  |

# iW Graze QLX Powercore

## Application Conditions

Ambient temperature range -20 to +50 °C


## Product Data

Full product code 871829160982799  
Order product name BCS437 30x60/2700-6500 L305  
EAN/UPC – product 8718291609827  
Order code 523-000079-23  
SAP numerator – quantity per pack 1

|                                 |   |
|---------------------------------|---|
| Numerator – packs per outer box | 4   |
| SAP material                    | 910503703667  |
| SAP net weight (piece)          | 0.345 kg  |
| Commercial Code                 | 523-000079-23   |
| Commercial Code                 | iW Graze QLX Powercore, 30° x 60° Beam Angle, 305 mm (1 ft) |



## Dimensional drawing



Graze

