



# iW Graze QLX Powercore

iW Graze QLX Powercore, 15° x 30° Beam Angle, 1219 mm (4 ft)

iW Graze QLX Powercore, 15° x 30° Beam Angle, 1219 mm (4 ft)

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze QLX Powercore is capable of illuminating over 10 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

## Product data

| General Information           |                               | Controls and Dimming         |                                                                                                                                                                              |
|-------------------------------|-------------------------------|------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Lamp family code              | LED-HB [ LED High Brightness] | Dimmable                     | Yes                                                                                                                                                                          |
| Light source replaceable      | No                            |                              |                                                                                                                                                                              |
| Driver included               | Yes                           | Mechanical and Housing       |                                                                                                                                                                              |
| Luminaire light beam spread   | 15° x 30°                     | Length                       | 1219 mm                                                                                                                                                                      |
| Protection class IEC          | Safety class I (I)            | Approval and Application     |                                                                                                                                                                              |
| CE mark                       | CE mark                       | Ingress protection code      | IP66 [ Dust penetration-protected, jet-proof]                                                                                                                                |
| UL mark                       | UL mark                       | Mech. impact protection code | IK10 [ 20 J vandal-resistant]                                                                                                                                                |
| Lifetime to 70% luminous flux | 100000 h                      | Vibration standard           | Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations. |
| Operating and Electrical      |                               | Vibration rating             | Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please                                                                           |
| Input Voltage                 | 100 to 277 V                  |                              |                                                                                                                                                                              |
| Input frequency               | 50 to 60 Hz                   |                              |                                                                                                                                                                              |

## iW Graze QLX Powercore

contact your Color Kinetics Lighting Sales rep for custom configurations.

### Initial Performance (IEC Compliant)

Initial input power 60 W

### Application Conditions

Ambient temperature range -20 to +50 °C


### Product Data

Full product code 871829160964300  
Order product name BCS437 15x30/2700-6500 L1219

|                                   |                                                              |
|-----------------------------------|--------------------------------------------------------------|
| EAN/UPC – product                 | 8718291609643                                                |
| Order code                        | 523-000079-37                                                |
| SAP numerator – quantity per pack | 1                                                            |
| Numerator – packs per outer box   | 1                                                            |
| SAP material                      | 910503703681                                                 |
| SAP net weight (piece)            | 4.700 kg                                                     |
| Commercial Code                   | 523-000079-37                                                |
| Catalogue number description      | iW Graze QLX Powercore, 15° x 30° Beam Angle, 1219 mm (4 ft) |



## Dimensional drawing



Graze

