



# eW Graze MX Powercore

**eW Graze MX Powercore, 4000 K, 30° x 60° Beam Angle, 914 mm (3 ft)**

eW Graze MX Powercore, 4000 K, 30° x 60° Beam Angle, 914 mm (3 ft)

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

## Product data

General information		Operating and electrical	
Lamp family code	LED-HB [ LED High Brightness]	Input Voltage	100 to 277 V
Light source colour	Neutral white	Input frequency	50 to 60 Hz
Light source replaceable	No	Controls and dimming	
Driver included	Yes	Dimmable	Yes
Luminaire light beam spread	30° x 60°	Mechanical and housing	
Protection class IEC	Safety class I (I)	Housing material	Aluminum extruded
CE mark	CE mark	Optical cover/lens material	Polycarbonate
UL mark	UL and cUL mark	Length	914 mm
Lifetime to 50% luminous flux	60000 h		
Lifetime to 70% luminous flux	60000 h		

eW Graze MX Powercore

Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	2325 lm
Initial LED luminaire efficacy	57.8 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial input power	42 W

Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C	60000
Reported	
Lumen Maintenance 50% at 50 °C	60000
Reported	

Lumen Maintenance 70% at 25 °C	60000
Reported	
Lumen Maintenance 70% at 50 °C	60000
Reported	

Application conditions	
Ambient temperature range	-20 to +50 °C

Product data	
Full product code	871829161053300
Order product name	BCS419 30x60/4000 L914
EAN/UPC – product	8718291610533
Order code	523-000080-40
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703728
Net Weight (Piece)	3.800 kg
Commercial Code	523-000080-40
Catalogue number description	eW Graze MX Powercore, 4000 K, 30° x 60° Beam Angle, 914 mm (3 ft)



Dimensional drawing

