



eW Graze QLX Powercore

BCS427 30x60/5500 L914

eW Graze QLX Powercore, 5500 K, 30° x 60° Beam Angle, 914 mm (3 ft)

Many architectural structures need a linear fixture capable of illuminating several storeys with minimal setback and reduced power consumption. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze QLX Powercore is capable of illuminating over 10 metres at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General Information		Input frequency	
Lamp family code	LED-HB [LED High Brightness]	50 to 60 Hz	
Lamp colour code	Cool white	Controls and Dimming	
Light source replaceable	No	Dimmable	Yes
Driver included	Yes	Mechanical and Housing	
Optical cover/lens type	PCC [Polycarbonate bowl/cover clear]	Housing material	Aluminum extruded
Luminaire light beam spread	30° x 60°	Optical cover/lens material	Polycarbonate
Protection class IEC	Safety class I (I)	Length	914 mm
CE mark	CE mark	Colour	Aluminium
UL mark	UL and cUL mark	Approval and Application	
Lifetime to 70% luminous flux	100000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Operating and Electrical		Mech. impact protection code	IK10 [20 J vandal-resistant]
Input Voltage	100 to 277 V		

eW Graze QLX Powercore

Vibration standard	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.
Vibration rating	Not compliant to ANSI C136.31, 3G. Special orders are available to conform to the standard. Please contact your Color Kinetics Lighting Sales rep for custom configurations.

Initial Performance (IEC Compliant)

Lamp colour temperature	5500 K
Initial input power	42 W

Over Time Performance (IEC Compliant)

Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Reported	60000

Application Conditions	
Ambient temperature range	-40 to +50 °C
Product Data	
Full product code	871829161144800
Order product name	BCS427 30x60/5500 L914
EAN/UPC – product	8718291611448
Order code	523-000081-41
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703788
SAP net weight (piece)	3.800 kg
Commercial Code	523-000081-41
Commercial Code	eW Graze QLX Powercore, 5500 K, 30° x 60° Beam Angle, 914 mm (3 ft)



Dimensional drawing

