



# eColor Reach Powercore gen2

## DCP775 BL 100-240V

Blue - 100 to 240 V - 5°

eColor Reach Powercore gen2 high-performance LED luminaires are premium exterior long-throw dynamic high-quality solid color luminaires for lighting tall buildings, bridges, and iconic structures. A full range of accessories allow for customizable beam angles for floodlighting, spotlighting, wall washing, and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

### Product data

General Information		Controls and Dimming	
Lamp family code	LED-HB [ LED High Brightness]	Dimmable	Yes
Light source color	Blue	<b>Mechanical and Housing</b>	
Light source replaceable	No	Housing Material	Aluminum
Driver included	Yes	Optic material	Glass
Luminaire light beam spread	5°	<b>Approval and Application</b>	
Protection class IEC	Safety class I	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Type description	-	<b>Initial Performance (IEC Compliant)</b>	
CE mark	CE mark	Initial luminous flux (system flux)	8937 lm
UL mark	UL mark	Initial LED luminaire efficacy	30.8 lm/W
Lifetime to 70% luminous flux	70000 h	Initial input power	250 W
Operating and Electrical			
Input Voltage	100 to 240 V		
Input Frequency	50 to 60 Hz		

## eColor Reach Powercore gen2

### Application Conditions


Ambient temperature range -40 to +50 °C

### Product Data

Full product code 871829138438000  
Order product name DCP775 BL 100-240V  
EAN/UPC - Product 8718291384380  
Order code 910503703942

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503703942
Net Weight (Piece)	34.000 kg

### Dimensional drawing



Reach

