



eColor Graze MX Powercore

BCS439 60x30 RB L305

Royal blue - 60° x 30° - 305 mm - Aluminium

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Product data

General Information		Input frequency	
Lamp family code	LED-HB [LED High Brightness]	50 to 60 Hz	
Lamp colour code	Royal blue	Controls and Dimming	
Light source replaceable	No	Dimmable	Yes
Driver included	Yes	Mechanical and Housing	
Optical cover/lens type	PCC [Polycarbonate bowl/cover clear]	Housing material	Aluminum extruded
Luminaire light beam spread	60° x 30°	Optic material	Polycarbonate
Protection class IEC	Safety class I (I)	Optical cover/lens material	Polycarbonate
Glow-wire test	850/5 [Temperature 850 °C, duration 5 s]	Length	305 mm
CE mark	CE mark	Colour	Aluminium
UL mark	UL mark	Approval and Application	
Lifetime to 70% luminous flux	100000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Operating and Electrical		Mech. impact protection code	IK10 [20 J vandal-resistant]
Input voltage	100 to 277 V		

eColor Graze MX Powercore

Application Conditions

Ambient temperature range -20 to +50 °C


Product Data

Full product code 871829160561499
Order product name BCS439 60x30 RB L305
EAN/UPC – product 8718291605614
Order code 910503703998

Numerator – quantity per pack 1
Numerator – packs per outer box 4
Material no. (12NC) 910503703998
Net weight (piece) 1.200 kg

850°C

Dimensional drawing



Graze

